

# NEWSLETTER FEBRUARY 2012

## Our staff of the final control

Together in a small team lead our Lady`s final inspection of our products. They control and package the finished products according to quality control according to internal documents based on AQL reports. And here they are:



**Mrs. Sonja Ackermann** (right)  
- Since 2000 by RUBA Thermoplast AG  
- Ensuring quality control  
- Responsible for the warehouse  
- Support the production manager

**Mrs. Melanie Jaworski** (left)  
- Since 2010 with us  
- Control and packaging

**Mrs. Binnur Dinc** (left)  
- Since 2008 by RUBA Thermoplast AG  
- Control and packaging  
- Support of Mrs. Ackermann

**Mrs. Iris Nussbaum** (right)  
- Since 2008 with us  
- Support of Mrs. Ackermann  
- Quality monitoring



## Change of personnel and new commercial trainee



End of 2011 left us **Mrs. Linda Pauli** from the production. We thank her for the good cooperation and wish her all the best for the future professionally as well as personally...

Hereby we are pleased to welcome **Mr. Kleyvson Xavier** as the first apprentice at our company. The next three years of training will be for him very instructive.



We hope, that he will be a future qualified force of our company and wish him a lot of succes and fulfillment!

## 24-Cavity Mold

The increasing demand and the number of produced standard caps for Ø30 mm tubes in the last years, was the reason why we produce a new form.

The new form has **24 cavities** and doubling the annual production capacity. For the future we expect competitive pricing, which will be of course our customers benefit. This allows us even better quality of caps and especially shorter delivery times.

**And here the story in pictures ...**



## Combi Cap

The first combi caps has RUBA already developed in the year 2007. The cosmetic industry uses our combi caps for various products and can be bought almost everywhere.

The combi cap consists of two parts:

**TA - lower part** and **SK - top part- over cap** and ist in following diameters available:

**Ø 22 mm, Ø 25 mm und Ø 30 mm**



Together with our clients, we made a few improvements and we currently use different material for the production:

TA	Total PPH 5060	Moplen MFI7.5	
SK	LG SAN	K-Resin	NAS 21